

Mitutoyo**Digital depth gauge AOS with data output, Measuring range: 150mm****Order data**

Order number	418711 150
GTIN	4946368688503
Item class	44A

Description**Version:**

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cables No. 497080 and 497100.

Technical description

Bridge length	100 mm
Calibration	A1
Scale divisions	0.01 mm
Interface	USB interface
Interface	Digimatic interface
Cross-section measuring beam	16×3.5 mm
#Article no of the battery / rechargeable battery fitted	081560 357
#Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm

Standard	ISO 13385
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	Wallet
Measurement method of the measuring instrument	electro-magnetic inductive procedure
Type of product	Depth gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/418711-150>