

**Garant**
**Tool24 Smartline – cabinet system including dividing material, Type: S11M**

**Order data**

Order number	979001 S11M
GTIN	4062406133801
Item class	9SA

**Description**
**Version:**

Flexible industrial vending solution for storage and management of machining and assembly tools, measuring tools, protective workwear and many other consumable items. The master system can be extended and combined with additional extension systems of any Tool24 hardware variants. The individual software packages allow the systems to be tailored to your exact requirements.

Body and doors made of 1 mm sheet metal. Pallet truck base made of 1.75 mm sheet metal. Storage shelf made of bamboo. This article is compatible with the Hoffmann Group Connected software solutions.

**Advantage:**
**Hoffmann Group Connected**

With this article you are gaining a building block for your digitally networked production. Increased productivity can be achieved together with the respective software module.

**Application:**

Automatic industrial vending solution for storage and management of tools and C-items.

**Content:**

Dividers: 10 pcs. No. 960310 size 4+18; 1 pc. No. 960330 size 3+14

**Fitted with:**

Number of drawers × drawer front height: 1 technical drawer

10×75 mm; 1×150 mm

**Supplied with:**

Master system: Tool issuing cabinet with 11 drawers 36×36 U, touch screen, barcode scanner, PC including BASIC software package and dividers.

**Supplied with:**

Touch screen 22 inch, barcode scanner, PC including BASIC software package

**Colour:**

Body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated.**

## Technical description

Type	Basic master cabinet, complete
Division within a drawer	36×36 U
Drawer/pull-out shelf load capacity	75 kg
Depth	750 mm
Weight	249 kg
Drawer usable width	612 mm
Storage area	4 m <sup>2</sup>
Drawer usable depth	612 mm
Number of drawers	11
Width	717 mm
Height	1390 mm
Series	Tool24 Smartline
Series	Hoffmann Group Connected
Series	Tool24 Smartline
Interface	Hoffmann Group Connected
Drawer runner extension	Anti-tilt lock
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system