



## Digital external micrometer with offset measuring faces, Measuring range: 0-25mm



### Order data

Order number	421681 0-25
GTIN	4059192058715
Item class	43A

### Description

#### Version:

Innovative external micrometer with **10 mm tall characters** on sharp contrast display. Practical HOLD function for freezing the measured value for reliable, error-free reading. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position. A well-arranged **tolerance display with additional warning limits** allows the user to recognise whether the workpiece is within the tolerance limits. Measuring spindle and anvil carbide tipped.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032, 1 setting standard from size 25-50.

#### Optional extras:

Data cable No. 498941.

### Technical description

Digit height LCD display	10 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Scale divisions	0.00005 in
Number of batteries contained	1

Error limit	4 µm
Calibration	B1
Scale divisions	0.001 mm
Spindle pitch	0.5 mm
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Interface	RS232C interface
Measurement technology	digital
Packaging	sturdy box
Reversible reading	mm / inch
Type of product	External micrometer

## Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------