

**Mitutoyo**
**Digital external micrometer with data output, Measuring range: 0-30mm**

**Order data**

Order number	421590 0-30
GTIN	4946368736693
Item class	44A

**Description**
**Version:**

Error limits more accurate than the requirements of **DIN 863**. **On / Off, Origin (basic setting), Zero / Abs** (for zeroing in any position), **Hold / Data** (save measurement value or send data).

**Description:**

- **Spindle pitch 10 mm per revolution reduces the approach time.**
- **Non-rotating spindle protects the surfaces being measured.**
- **Absolute measuring system. No need to set zero point after switching on. Prevents measurement errors.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357. 1 micrometer standard from size 25-55.

**Optional extras:**

Data cable No. 497445.

**Technical description**

Scale divisions	0.001 mm
Error limit	2 µm
Calibration	B1
Spindle pitch	10 mm
Measuring range	0 - 30 mm

Number of batteries contained	1
Series	QuickMike
Article no of the battery / rechargeable battery fitted	081560 357
Spindle Ø	6.35 mm
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

## Services

Calibration External micrometer without setting dimension maximum measuring range 100 mm	022000 100
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

## Accessories

Connecting cable with data switch Type D1	497445 D1
Connecting cable with data switch Type D2	497445 D2
Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type USB2	497445 USB2