

Garant**Tool24 PickOne – master system DE, Total number of compartments: 448****Order data**

Order number	979201 448
GTIN	4062406134105
Item class	9SA

Description**Version:**

Goods issuing system with innovative drum system to ensure secure individual withdrawal of every item. Very quick goods removal due to low access times, self-opening compartment and visual signal at the correct withdrawal compartment. The drum of the Tool24 PickOne is available with up to 4 different compartment sizes as standard configuration and with a load capacity of more than 1000 kg, specially designed for industrial use. Flexible attachment of a touch screen thanks to double-sided perforated panel.

The master system can be extended with additional extension systems and combined with all Tool24 hardware variants.

This article is compatible with the Hoffmann Group Connected software solutions. 4 compartment variants, ideal for discharging different sized items and changing item portfolios.

Advantage:**Hoffmann Group Connected**

With this article you are gaining a building block for your digitally networked production. Increased productivity can be achieved together with the respective software module.

Supplied with:

Touch screen 22 inches, barcode scanner, PC including Basic software package.

Colour:

Body RAL 7035 light grey, fronts RAL 7016 anthracite grey, **powder-coated.**

Note:

The drum of the Tool24 PickOne is individually and uniquely configurable for each customer with 4 different storage sizes depending on the portfolio of items to be issued. Talk to your technical adviser.

The weights do not include a PC and monitor.

Technical description

Width	1080 mm
Number of compartments A	320
Height	2000 mm
Number of compartments D	32
Weight	275 kg
Number of compartments C	64
Number of compartments B	32
Depth	875 mm
Load capacity per compartment	2 kg
Series	Tool24 PickOne
Series	Hoffmann Group Connected
Series	Tool24 PickOne
Interface	Hoffmann Group Connected
Cabinet housing internal load capacity	1000 kg
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system