



Digital external micrometer for curved surfaces, Measuring range: 0-25mm



Order data

Order number	421683 0-25
GTIN	4059192058685
Item class	43A

Description

Version:

Innovative external micrometer with **10 mm tall characters** on sharp contrast display. Practical HOLD function for freezing the measured value for reliable, error-free reading. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position. A well-arranged **tolerance display with additional warning limits** allows the user to recognise whether the workpiece is within the tolerance limits.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032, 1 setting standard from size 25-50.

Optional extras:

Data cable No. 498941.

Technical description

Scale divisions	0.00005 in
Calibration	B1
Error limit	4 µm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Scale divisions	0.001 mm
Digit height LCD display	10 mm

Number of batteries contained	1
Spindle pitch	0.5 mm
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Interface	RS232C interface
Measurement technology	digital
Packaging	sturdy box
Reversible reading	mm / inch
Type of product	External micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25