

**Garant****Tool24 Smartline – upright cabinet fitted with tool sockets, for tool shanks: HSK100****Order data**

Order number	979101 HSK100
GTIN	4062406134082
Item class	9SA

**Description****Version:**

The pull-out shelves are supported from the base and equipped with central locking (can be used for emergency release). The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool stands, carrying rails, storage shelf trays, and perforated tool boards. The pull-out frames are equipped with an anti-tilt device. The pull-out frames open automatically. This ensures quick access to the tools.

- **Storage of pre-set tools.**
- **Only for use in conjunction with a Tool24 Smartline Master Unit system.**
- **Available with 14 different configurations (for different tool shanks SK, VDI, C, HSK).**
- **Supplied with 24 carrier rails.**
- **Mountings suitable for tool stands, support rails, shelf trays and perforated tool panels.**
- **Distributed safe working load per pull-out frame: 600 kg.**
- **Maximum upright cabinet load: 2400 kg.**
- **Locking system for emergency release.**

**Application:**

Automatic industrial vending solution for storage and management of tools and C-items.

**Colour:**

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

**Note:**

Upright cabinets place increased demands on the floor, since the pull-out frames run directly on the floor! The following pre-requirements for the installation site must be satisfied absolutely by the customer:

- **Flatness tolerance for finished floors as per DIN 18202.**
- **Angularity of a maximum of 2 millimetres over the measurement length of 1 metre.**
- **The subsurface must have a sufficient load-bearing capacity.**
- **Only place on ground that is absolutely level.**

The systems are prepared for wall or floor-mounting and must be secured against tilting. These upright cabinets can only be used in conjunction with a Tool24 Smartline Master Unit system No. 979001 S11M or No. 979001 S11M-EN, Tool24 PickOne Master Unit system No. 979201 DE or No. 979211 EN, and Tool24 Locker Master Unit system No. 979300 DE or No. 979310 EN.

## Technical description

Height	2000 mm
Weight	320 kg
Number of pull-out frames	4
Vertical pull-out frame usable height	1750 mm
Vertical pull-out frame load capacity	600 kg
Number of tool carriers No. 970130	24
Depth	750 mm
Number of tool sockets	120
Width	717 mm
Pull-out frame drawers width	155 mm
Axial spacing A	127 mm
Series	Tool24 Smartline
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system

**Accessories**

Tool carrier with tool sockets for tool shanks HSK100	970130 HSK100
---	---------------