

**Cordless hammer drill / driver without battery or charger, Type: GSB1860PRO****Order data**

Order number	070113 GSB1860PRO
GTIN	
Item class	03B

**Description****Version:**

**Bosch cordless hammer drill / driver** for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

With **brushless EC motor**.

**Kick-back control** with automatic shut-down if jammed, together with unique precision clutch.

Compact design, very short head length (only 184 mm) for perfect handling (size GSB1890C), therefore ideal for working in restricted spaces. Can be retrofitted with a connectivity module.

With motor brake.

**Advantage:**

Very short head length of only 184 mm.

**Supplied with:**

**Without battery**, without charger and with L-BOXX.

**Note:**

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

## Technical description

Battery voltage	18 V
Manufacturer's designation	GSB 18V-60C
typical application	Strong
maximum twist drill size Ø in steel	10 mm
maximum speed 2nd speed	1900 min <sup>-1</sup>
maximum vibration to EN without hammer drill function	2.5 m/s <sup>2</sup>
maximum twist drill size Ø in concrete	10 mm
maximum torque hard	60 Nm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.8 kg
Packaging	Modular case (L-Boxx)
Motor design	Brushless motor
maximum twist drill size Ø in wood	38 mm
maximum speed 1st speed	0 - 600 min <sup>-1</sup>
maximum torque soft	31 Nm
maximum vibration to EN with hammer drill function	8 m/s <sup>2</sup>
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Steel
Suitable for material	wood
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

---

## Accessories

Battery starter setProCore Battery type, battery voltage C18  
V

073863 C18

Li-ion batteryProCore Battery type, battery voltage C18 V

073856 C18