

**Cordless hammer drill / driver ProCORE, Manufacturer ID: GSB1860PRO****Order data**

Order number	070112 GSB1860PRO
GTIN	3165140951432
Item class	03B

Description**Version:**

Bosch cordless hammer drill / driver for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

With **brushless EC motor**.

Kick-back control with automatic shut-down if jammed, together with unique precision clutch. Compact design, very short head length (only 184 mm) for perfect handling (size GSB1860PC), therefore ideal for working in restricted spaces. Can be retrofitted with a connectivity module.

Supplied with:

Supplied with **2x ProCORE 18 V 4.0 Ah** Li-ion battery, charger, and L-BOXX.

Note:

See No. 073851 ff. and 073866 ff for suitable spare batteries and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GSB 18V-60C

Battery capacity: 4 A·h

Battery voltage: 18 V

Motor design: Brushless motor

maximum torque soft: 31 N·m

maximum torque hard: 60 N·m

Technical description

maximum torque hard	60 N·m
Battery voltage	18 V
maximum vibration to EN without hammer drill function	2.5 m/s ²
maximum speed 1st speed	0 - 600 rpm
Motor design	Brushless motor
maximum twist drill size Ø in steel	10 mm
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.8 kg
maximum vibration to EN with hammer drill function	8 m/s ²
suitable battery - supplier / battery type / voltage	Bosch 18 V
Packaging	Modular case (L-Boxx)
maximum twist drill size Ø in wood	38 mm
maximum twist drill size Ø in concrete	10 mm
maximum torque soft	31 N·m
Manufacturer's designation	GSB 18V-60C
typical application	Strong
maximum speed 2nd speed	1900 rpm
Battery capacity	4 A·h
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion

Accessories

Li-ion battery ProCore Battery type, battery voltage C18 V

073856 C18

Battery starter set ProCore Battery type, battery voltage
C18 V

073863 C18