

**Cordless drill / driver ProCORE, Type: GSR1860PRO****Order data**

| | |
|--------------|-------------------|
| Order number | 070245 GSR1860PRO |
| GTIN | |
| Item class | 03B |

Description**Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Kick-back control with automatic shut-down if jammed, together with unique precision clutch and motor brake. 13 mm auto-lock metal drill chuck. High torque.

Can be retrofitted with a **connectivity** module.

Advantage:

Electronic Motor Protection.

Supplied with:

Supplied with 2x ProCORE 18V 4.0 Ah Li-ion batteries, quick charger, L-BOXX.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GSR 18V-60C

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 4 A·h

Battery voltage: 18 V

Motor design: Brushless motor

Technical description

| | |
|--|------------------------------|
| maximum torque soft | 31 N·m |
| maximum twist drill size Ø in steel | 13 mm |
| Packaging | Modular case (L-Boxx) |
| maximum torque hard | 60 N·m |
| Manufacturer's designation | GSR 18V-60C |
| typical application | Strong |
| maximum twist drill size Ø in wood | 38 mm |
| suitable battery - supplier / battery type / voltage | Bosch 18 V |
| Weight | 1.8 kg |
| Motor design | Brushless motor |
| maximum vibration to EN | <2.5 m/s ² |
| Speed range 1st speed | 0 - 600 min ⁻¹ |
| Quick-clamping chuck range | 1.5 - 13 mm |
| Battery capacity | 4 A·h |
| Battery voltage | 18 V |
| Speed range 2nd speed | 0 - 1900 min ⁻¹ |
| Number of rechargeable batteries contained | 2 |
| Type of rechargeable battery | Lithium-ion |
| Power supply | Rechargeable battery-powered |
| Suitable for material | wood |
| Suitable for material | Steel |
| Type of product | Drill/driver |
| USP1 | 18V |

USP2

Brushless motor, quick-change chuck
clamping range 1.5-13, in L-Boxx

Accessories

Battery starter set ProCore Battery type, battery voltage
C18 V

073863 C18

Li-ion battery ProCore Battery type, battery voltage C18 V

073856 C18