

**Cordless drill / driver without battery, Type: GSR1860C****Order data**

Order number	070246 GSR1860C
GTIN	
Item class	03B

Description**Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Can be retrofitted with a **connectivity** module.

Advantage:

Electronic Motor Protection.

Standard:

- **Compact, powerful cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Supplied with:

Cordless Concept impact wrench **without battery**, without charger and with L-BOXX.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Technical description

Speed range 2nd speed	0 - 1900 min ⁻¹
Number of rechargeable batteries contained	0
Speed range 1st speed	0 - 600 min ⁻¹
Manufacturer's designation	GSR 18V-60C
typical application	Strong
Packaging	Modular case (L-Boxx)
maximum torque hard	60 Nm
Quick-clamping chuck range	1.5 - 13 mm
maximum torque soft	31 Nm
Battery voltage	18 V
maximum twist drill size Ø in steel	13 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	1.8 kg
Motor design	Brushless motor
maximum twist drill size Ø in wood	38 mm
maximum vibration to EN	<2.5 m/s ²
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	18V
USP2	Brushless motor, with softgrip, without battery, in L-Boxx

Accessories

Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B18 V	073854 B18