

Garant**Shelf ladder, mobile, Number of steps: 13****Order data**

Order number	935800 13
GTIN	4062406134242
Item class	91B

Description**Version:**

Mobile single ladder with extra wide rungs for attachment to racking. When not in use the ladder can be stowed on the racking out of the way. Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Supplied with Easyfix mounting. With 2 self-arresting brake rollers, Ø 80 mm. Smooth-running movement support at the top.

Colour:

Stiles anthracite RAL 7016 **powder-coated**.

Note:

Each ladder is **made to order**.

The **maximum vertical attachment height must always be stated**.

Technical description

maximum vertical attachment height up to	3.67 m
Weight	13.24 kg
Ladder length	3.5 m
outer width at bottom	0.6 m

Number of steps	13
Cross beam height	25 mm
Cross beam width	73 mm
Step height	235 mm
Throat	1.4 m
Working height approx. suitable for racking height	4.4 m 3000 mm
Type of product	Shelf ladder

Accessories

Anodised aluminium tube, 3000 mm long Type 1	935810 1
Bracket with end stop Type L	935812 L
GripStep step overlay suitable for ladder size 13	935820 13
Intermediate bracket for aluminium tube Type 1	935811 1
Bracket with end stop Type R	935812 R