

**Garant****Shelf ladder, mobile, Number of steps: 11****Order data**

Order number	935800 11
GTIN	4062406134235
Item class	91B

**Description****Version:**

Mobile single ladder with extra wide rungs for attachment to racking. When not in use the ladder can be stowed on the racking out of the way. Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Supplied with Easyfix mounting. With 2 self-arresting brake rollers, Ø 80 mm. Smooth-running movement support at the top.

**Colour:**

Stiles anthracite RAL 7016 **powder-coated**.

**Note:**

Each ladder is **made to order**.

The **maximum vertical attachment height must always be stated**.

**Technical description**

Ladder length	2.95 m
Weight	11.5 kg
outer width at bottom	0.6 m
maximum vertical attachment height up to	3.11 m

Number of steps	11
Cross beam height	25 mm
Step height	235 mm
Cross beam width	73 mm
Throat	1.2 m
Working height approx. suitable for racking height	3.95 m 3000 mm
Type of product	Shelf ladder

---

## Accessories

Bracket with end stop Type R	935812 R
Bracket with end stop Type L	935812 L
GripStep step overlay suitable for ladder size 11	935820 11
Intermediate bracket for aluminium tube Type 1	935811 1
Anodised aluminium tube, 3000 mm long Type 1	935810 1