

Garant**Shelf ladder, mobile, Number of steps: 7****Order data**

Order number	935800 7
GTIN	4062406134211
Item class	91B

Description**Version:**

Mobile single ladder with extra wide rungs for attachment to racking. When not in use the ladder can be stowed on the racking out of the way. Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Supplied with Easyfix mounting. With 2 self-arresting brake rollers, Ø 80 mm. Smooth-running movement support at the top.

Colour:

Stiles anthracite RAL 7016 **powder-coated**.

Note:

Each ladder is **made to order**.

The **maximum vertical attachment height must always be stated**.

Technical description

maximum vertical attachment height up to	2.11 m
Number of steps	7
outer width at bottom	0.6 m
Weight	8.9 kg

Ladder length	1.85 m
Step height	235 mm
Throat	0.85 m
Cross beam height	25 mm
Working height approx.	3 m
Cross beam width	73 mm
suitable for racking height	2000 mm
Type of product	Shelf ladder

Accessories

GripStep step overlay suitable for ladder size 7	935820 7
Bracket with end stop Type L	935812 L
Bracket with end stop Type R	935812 R
Intermediate bracket for aluminium tube Type 1	935811 1
Anodised aluminium tube, 3000 mm long Type 1	935810 1