



Electronics side cutter Super Knips® VDE insulated, KW, overall length: 125mm



Order data

Order number	726653 125
GTIN	4003773084099
Item class	73F

Description

Version:

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

Plastic-coated handles to **DIN EN 60900 / VDE 0682-201 insulated for working at voltages up to 1000 V.**

Standard:

DIN ISO 9654

Material:

Made of stainless steel (INOX).

Technical description

Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
Cutter length	9 mm
Head width	13.5 mm
Cutting capacity medium-hard steel wire	0.2 - 1 mm
Cutting chamfer	without bevel
Material	Stainless steel, INOX
Standard	DIN ISO 9654
Handle	Multi-component covering

Product name attribute	KW
with return spring	yes
with wire holder	no
Type of product	Cutting pliers