



GKS compact linishing machine, Type: 790502004



Order data

Order number	077608 790502004
GTIN	4014586888279
Item class	03H

Description

Version:

Powerful compact linishing machine for deburring metal.

- **Very high operator safety, thanks to control of flying sparks.**
- **Very cost-effective as a procurement proposition, with optimum price-performance ratio.**
- **For immediate use. No setting up or installation necessary.**

Supplied with:

Supplied with 1x linishing belt 75×2000mm (K 36 R).

Note:

See No. 558310 for linishing belts.

Manufacturer's designation: GKS 75

AC supply voltage: 400 V

Power consumption: 1500 W

maximum speed: 3000 min⁻¹

Tape width: 75 mm

Band length: 2000 mm

Technical description

Weight	45 kg
Manufacturer's designation	GKS 75
Power consumption	1500 W
AC supply voltage	400 V
Band length	2000 mm
maximum speed	3000 min ⁻¹
Power supply	Mains-powered
Tape width	75 mm
Type of product	Linishing machine