



Cordless drill / driver, Type: M18CBLDD-2



Order data

Order number	070210 M18CBLDD-2
GTIN	4058546222628
Item class	03L

Description

Version:

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use. With low-maintenance brushless motor with high torque. **REDLINK™ electronics** – reliable load management with **overload protection** for long working life of the battery, motor and gearbox.

Advantage:

REDLINK™ electronics.

Supplied with:

Supplied with 2 pcs M18 Red Li-ion batteries, M12-18C charger, belt clip, transport case.

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

Manufacturer's designation	M18CBLDD-202C
----------------------------	---------------

maximum speed 1st speed	0 - 500 min ⁻¹
Weight	1.5 kg
Quick-clamping chuck range	1.5 - 13 mm
typical application	Strong
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum torque hard	60 Nm
maximum twist drill size Ø in steel	13 mm
Motor design	Brushless motor
maximum speed 2nd speed	1800 min ⁻¹
maximum twist drill size Ø in wood	52 mm
Battery capacity	2 Ah
Packaging	Carrying case
maximum vibration to EN	<2.5 m/s ²
Battery voltage	18 V
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver

Accessories

Offset screwdriving attachment Type WB1	073920 WB1
Offset screwdriving attachment Type OSD2	073920 OSD2
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M18B2 Battery type MB18	073827 MB18