

**LED cordless lamp 0 version without battery, 18 V, Type: GLI182200C****Order data**

Order number	073205 GLI182200C
GTIN	3165140953832
Item class	03B

**Description****Version:**

Sturdy cordless building site lamp 120°. Individual control and adjustment using **Bosch**

**Connectivity app.****Function:**

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

**Cordless lamp without battery and without charger.**

**Note:**

Suitable spare batteries and chargers can be found under No. 073851– 073866.

**Technical description**

Battery voltage	18 V
Illumination step 2	300 lm
IP Index of Protection	IP 64
Manufacturer's designation	GLI 18-2200C

Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	1900 g
Illumination	2200 lm
Power supply	Rechargeable battery-powered
Bulb	LED module
ATEX zone	no
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Work lamp

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type 1880CV	073866 1880CV