



Cordless drill / driver, Type: M18FDD2-2



Order data

Order number 070210 M18FDD2-2

GTIN

Item class 03L

Description

Version:

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use. Top model FUEL™ with **brushless POWERSTATE™ motor** for very high efficiency. **Very low wear** and up to 10 times the working life of standard DC motors. The high efficiency and the enhanced battery capacity permit **up to 2x longer operating times** (compared to other Li-ion technologies). **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

Advantage:

FUEL™ top model.

Supplied with:

Supplied with additional handle for easier support of the torque forces.

Supplied with 2x Red Li-ion batteries, with charger, belt clip, HD box (modular case).

Technical description

typical application	Heavy Duty
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum twist drill size Ø in steel	16 mm
maximum twist drill size Ø in wood	89 mm
Battery capacity	2 A·h
Motor design	Brushless motor
maximum vibration to EN	<2.5 m/s ²
Weight	2.1 kg
maximum speed 2nd speed	2000 min ⁻¹
Battery voltage	18 V
Manufacturer's designation	M18 FDD2
Packaging	Modular case (HD=Heavy Duty)
maximum speed 1st speed	0 - 550 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
maximum torque hard	135 N·m
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver

Accessories

Offset screwdriving attachment Type OSD2	073920 OSD2
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M18B2 Battery type MB18	073827 MB18
Offset screwdriving attachment Type WB1	073920 WB1

Cordless drill/driver without battery or charger Type
M18FDD2-2

070211 M18FDD2-2