

Garant GRIDLINE

Upright cabinet perforated panel with plain sheet metal swing doors, height mm / number of perforated panels: 2000/3**Order data**

Order number	942031 2000/3
GTIN	4062406135423
Item class	9GI

Description**NOTE: Colour selection possible****Version:**

Perforated panel upright cabinet in 30×28G

Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. With pull-out frames with □ 9×9mm at 37 mm intervals for mounting Easyfix hooks and holders, and perforated panel accessories. Perforated panels adjustable on a 50-mm grid. The perforated panels are arranged as telescopic sections, each equipped with a lock **so that only one perforated panel can ever be open at a time**. Load capacity per pull-out frame 80 kg. Usable area for each side of the pull-out frame is 2.1 m² (depth × height 635×1690 mm).

Colour:

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For suitable accessories such Easyfix hooks and holders see Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Vertical pull-out frame load capacity: 80 kg

Height: 2000 mm

Width: 750 mm
 Depth: 700 mm
 Width in G: 30
 Depth in G: 28
 Vertical pull-out frame usable height: 1690 mm

Technical description

Vertical pull-out frame usable height	1690 mm
Height	2000 mm
Depth in G	28
Weight	217 kg
Depth	700 mm
Number of perforated panels	3
Width in G	30
Width	750 mm
Vertical pull-out frame usable depth	635 mm
Vertical pull-out frame load capacity	80 kg
Type of cabinet	Base cabinet
Version	Perforated panel vertical cabinet
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Drawer runner extension	Anti-tilt lock
Door opening angle	250 °
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Upright cabinet

Accessories

Slide handle for GridLine Type GP11

914226 GP11