

Garant GRIDLINE

## Upright cabinet perforated panel with plain sheet metal swing doors, height mm / number of perforated panels: 2000/4



### Order data

Order number	942031 2000/4
GTIN	4062406135430
Item class	9GI

### Description

#### NOTE: Colour selection possible

#### Version:

Perforated panel upright cabinet in 30×28G

Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. With pull-out frames with □ 9×9mm at 37 mm intervals for mounting Easyfix hooks and holders, and perforated panel accessories. Perforated panels adjustable on a 50-mm grid. The perforated panels are arranged as telescopic sections, each equipped with a lock **so that only one perforated panel can ever be open at a time**. Load capacity per pull-out frame 80 kg. Usable area for each side of the pull-out frame is 2.1 m<sup>2</sup> (depth × height 635×1690 mm).

#### Colour:

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For suitable accessories such Easyfix hooks and holders see Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Vertical pull-out frame load capacity: 80 kg

Height: 2000 mm

Width: 1000 mm  
 Depth: 700 mm  
 Width in G: 40  
 Depth in G: 28  
 Vertical pull-out frame usable height: 1690 mm

## Technical description

Depth in G	28
Weight	272 kg
Height	2000 mm
Vertical pull-out frame load capacity	80 kg
Depth	700 mm
Vertical pull-out frame usable height	1690 mm
Vertical pull-out frame usable depth	635 mm
Width in G	40
Number of perforated panels	4
Width	1000 mm
Version	Perforated panel vertical cabinet
Type of cabinet	Base cabinet
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Drawer runner extension	Anti-tilt lock
Door opening angle	250°
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Upright cabinet

## Accessories

Slide handle for GridLine Type GP11

914226 GP11