

Garant GRIDLINE

**Upright cabinet perforated panel with Viewing window swing doors, Height: 2000mm****Order data**

Order number	942043 2000
GTIN	4062406135478
Item class	9GI

**Description****Version:**

Perforated panel upright cabinet in 40×28G

Version as described under No. 942033 size 2000/4 but with **3 pull-out frames**. Outstandingly suitable for space-saving storage of lifting tackle and slings.

**Supplied with:**

3 pc. storage trays for slings No. 942054 size 2; 4 pc. universal holders 45° No. 955590 size 75; 4 pc. universal holders 90° No. 955600 size 100×100.

**Colour:**

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Technical description**

Depth in G	28
Number of perforated panels	3
Width	1000 mm
Vertical pull-out frame load capacity	80 kg

Weight	243 kg
Width in G	40
Vertical pull-out frame usable depth	635 mm
Vertical pull-out frame usable height	1690 mm
Height	2000 mm
Depth	700 mm
Type of cabinet	Base cabinet
Version	Perforated panel vertical cabinet
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Upright cabinet

---

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------