

Garant GRIDLINE

### Upright cabinet perforated panel with plain sheet metal swing doors, Height: 2000mm



#### Order data

Order number	942041 2000
GTIN	4062406135461
Item class	9GI

#### Description

##### Version:

Version as described under No. 942033 size 2000/4 but with **3 pull-out frames**. Outstandingly suitable for space-saving storage of lifting tackle and slings.

Swing doors reinforced on the inside and can be locked by 2-component Haptoprene slide handle with a cylinder lock. With pull-out frames with □ 9×9mm at 37 mm intervals for mounting hooks and supports, and perforated panel accessories. Perforated panels adjustable on a 50-mm grid. The perforated panels are arranged as telescopic sections, each equipped with a lock **so that only one perforated panel can ever be open at a time**. Load capacity per pull-out frame 80 kg. Usable area for each side of the pull-out frame is 2.1 m<sup>2</sup> (depth × height 635×1690 mm).

Perforated panel upright cabinet in 40×28G

##### Supplied with:

3 pc. storage trays for slings No. 942054 size 2; 4 pc. universal holders 45° No. 955590 size 75; 4 pc. universal holders 90° No. 955600 size 100×100.

##### Colour:

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Technical description

## Data sheet

Width in G	40
Height	2000 mm
Vertical pull-out frame usable depth	635 mm
Vertical pull-out frame load capacity	80 kg
Depth in G	28
Depth	700 mm
Weight	243 kg
Number of perforated panels	3
Vertical pull-out frame usable height	1690 mm
Width	1000 mm
Type of cabinet	Base cabinet
Version	Perforated panel vertical cabinet
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Upright cabinet

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/942041-2000>