

Garant GRIDLINE

Office Station complete, swing door with printer flap, 3 drawers, 2×30×28G, Type: DE



Order data

Order number	948800 DE
GTIN	4062406135515
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Contact point close to production for information, checking and documenting.

Top extension cabinet with lockable plastic roller shutter and the following equipment:

- **Integral lighting with LED technology.**
- **On/off switch for the lighting.**
- **5 Schuko sockets.**
- **2 storage shelves, height-adjustable at 25 mm intervals. Usable width 1400 mm, usable depth 300 mm.**
- **Pull-out worktop (melamine-coated wood) with anti-roll lip at the back, and locking in the pulled-out position. Thickness 29 mm. Pull-out 150 mm.**
- **Integral cable duct and cable slots.**
- **Connection cable 7 m long.**
- **Fan with filter.**

Sub-frame with computer housing with lockable swing door with printer flap. Swing-door cabinet with pull-out shelf, usable width 580 mm, usable depth 480 mm. 3-way multiple socket outlet, 250 V / 16 A with ON/OFF switch, within the swing-door cabinet.

Sub-frame for tool cabinet with 100% full extension drawers (75 kg load capacity).

Colour:

Body RAL 7035 light grey, drawers, doors RAL 7016, anthracite **powder-coated**.

Note:

Plastic roller shutter, colour not configurable.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Height: 2200 mm

Width: 1500 mm

Depth: 700 mm

Drawer usable width: 650 mm

Drawer usable depth: 600 mm

Weight: 342 kg

Technical description

Depth	700 mm
Drawer runner extension (partial/full extension)	100 %
Drawer usable depth	600 mm
Weight	342 kg
Width	1500 mm
Drawer usable width	650 mm
Drawer/pull-out shelf load capacity	75 kg
Height	2200 mm
Nominal voltage	250 V
Plug type, input	F
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	2x30x28G
Type of product	Office station

Accessories

Slide handle for GridLine Type HU12	914226 HU12
Lock plate for GridLine Type HU21	914227 HU21
Drawer, 75 kg Drawer front height 300 mm	931163 300