

Garant GRIDLINE

**Office Station complete, swing door with printer flap, 3 drawers, 2×30×28G,  
Type: DE****Order data**

Order number	948800 DE
GTIN	4062406135515
Item class	9GK

**Description****Version:**

Contact point close to production for information, checking and documenting.

Top extension cabinet with lockable plastic roller shutter and the following equipment:

- **Integral lighting with LED technology.**
- **On/off switch for the lighting.**
- **5 type F plug sockets.**
- **2 storage shelves, height-adjustable at 25 mm intervals. Usable width 1400 mm, usable depth 300 mm.**
- **Pull-out worktop (melamine-coated wood) with raised edge at the back, and locking in the pulled-out position. Thickness 29 mm. Pull-out 150 mm.**
- **Integral cable duct and cable slots.**
- **Connection cable 7 m long.**
- **Fan with filter.**

Sub-frame with computer housing with lockable swing door with printer flap. Swing-door cabinet with pull-out shelf, usable width 580 mm, usable depth 480 mm. 3-way multiple socket outlet, 250 V / 16 A with ON/OFF switch, within the swing-door cabinet.

Sub-frame for tool cabinet with 100% full extension drawers (75 kg load capacity).

**Colour:**

Body RAL 7035 light grey, drawers, doors RAL 7016, anthracite **powder-coated**.

**Note:**

Plastic roller shutter, colour not configurable.

---

**Technical description**

Depth	700 mm
Drawer runner extension (partial/full extension)	100 %
Drawer usable depth	600 mm
Weight	342 kg
Width	1500 mm
Drawer usable width	650 mm
Drawer/pull-out shelf load capacity	75 kg
Height	2200 mm
Nominal voltage	250 V
Plug type, input	F
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	2×30×28G
Type of product	Office station

---

**Accessories**

Slide handle for GridLine Type HU12	914226 HU12
Lock plate for GridLine Type HU21	914227 HU21
Drawer,75 kg Drawer front height 300 mm	931163 300