

Garant**Shelving cabinet with Viewing window swing doors, Height: 1000mm****Order data**

Order number	945003 1000
GTIN	4062406135508
Item class	9GI

Description**Version:**

Shelf cabinet in 30×11G. Mountings for storage shelves at 25-mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock.

Colour:

Body RAL 7035 light grey.

Doors RAL 7016 anthracite, **powder coated.**

Note:

See No. 944061, 944065 for storage shelves for GridLine racking cupboards.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1000 mm
Electronic locking system can be retrofitted	yes
Cabinet fronts	Viewing window swing door

Weight	39 kg
Handle positioning	top
Usable height	845 mm
Width	750 mm
Width in G	30
Depth	275 mm
Depth in G	11
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------