



Universal hole saw without centre drill, Hole Ø: 68mm



Order data

Order number	788041 68
GTIN	4058546228743
Item class	76G

Description

Version:

Carbide teeth for a longer working life, even when drilling into dense materials. Wide and deep flutes for easy removal of the drilled core. Aggressive tooth geometry for up to 10x quicker drill progression in comparison to bi-metal hole saws. Ideal for use in the electronics area and installation area.

Application:

For drilling larger holes and breaking throughs in various materials: masonry, lightweight materials, plastics, and wood. Unsuitable for use in hard materials such as concrete, granite, natural stone and hard tiles with a hardness greater than 30 N/mm².

Note:

Use only with rotary drive (no impact).

Technical description

Number of cutting edges Z	3
maximum cutting depth	60 mm
For use on	Switch boxes, cavity wall boxes and distribution boxes, recessed lighting
Use with impact / without impact	not for impact drilling

Tool material	Carbide
Type of product	Hole saw