


**Carbide-tipped hammer drill, SDS-max, Ø×overall length: 25X320mm**

**Order data**

Order number	789204 25X320
GTIN	3165140961455
Item class	76K

**Description**
**Version:**
**Special carbide insert geometry for longer tool lives.**

TARGET TIP TECHNOLOGY – more severely angled tip: More precise drilling, no slipping on the surface, aggressive drilling in concrete steel and faster drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

**Application:**

For drilling concrete, natural stone, and masonry.

**Note:**

New generation SDS-max-8X with welded solid carbide head.

Shank: SDS Max

Flute length: 200 mm

**Technical description**

Ø	25 mm
Flute length	200 mm
overall length	320 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

