



Carbide-tipped hammer drill, SDS-max, Øxoverall length: 24X520mm



Order data

Order number	789204 24X520
GTIN	3165140961448
Item class	76K

Description

Version:

Special carbide insert geometry for longer tool lives.

TARGET TIP TECHNOLOGY – more severely angled tip: More precise drilling, no slipping on the surface, aggressive drilling in concrete steel and faster drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

New generation SDS-max-8X with welded solid carbide head.

Shank: SDS Max

Flute length: 400 mm

Technical description

overall length	520 mm
Ø	24 mm
Flute length	400 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

