



Carbide-tipped hammer drill, SDS-max, Øxoverall length: 30X520mm



Order data

| | |
|--------------|---------------|
| Order number | 789204 30X520 |
| GTIN | 3165140565738 |
| Item class | 76K |

Description

Version:

Special carbide insert geometry for longer tool lives.

TARGET TIP TECHNOLOGY – more severely angled tip: More precise drilling, no slipping on the surface, aggressive drilling in concrete steel and faster drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

New generation SDS-max-8X with welded solid carbide head.

Shank: SDS Max

Flute length: 400 mm

Technical description

| | |
|----------------------------------|-----------------|
| overall length | 520 mm |
| Ø | 30 mm |
| Flute length | 400 mm |
| Tool material | Carbide |
| Use with impact / without impact | Impact drilling |
| Shank | SDS Max |
| Type of product | Masonry drill |

