

Garant
Carbide-tipped hammer drill SDS-plus, Ø×overall length: 12X160mm

Order data

| | |
|--------------|---------------|
| Order number | 789040 12X160 |
| GTIN | 4062406135720 |
| Item class | 71C |

Description
Version:

Drill head with square cross-section. **4×90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially** shaped **reinforcement protection**: prevents jamming when hitting reinforcements and increases the working life. Sturdy **single-piece** carbide head with 4 cutters, inserted as a solid item in the core of the drill. Significantly reduced risk of breakage.

Advantage:

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4×4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

Technical description

| | |
|----------------------------------|-----------------|
| Ø | 12 mm |
| Flute length | 110 mm |
| overall length | 160 mm |
| Tool material | Carbide |
| Use with impact / without impact | Impact drilling |
| Shank | SDS Plus |
| Type of product | Masonry drill |

