

## Garant

### Carbide-tipped hammer drill SDS-plus, Ø×overall length: 32X450mm



#### Order data

Order number	789040 32X450
GTIN	4062406135881
Item class	71C

#### Description

##### Version:

Drill head with square cross-section. **4×90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially** shaped **reinforcement protection**: prevents jamming when hitting reinforcements and increases the working life. **3-piece** sturdy carbide head with reinforced centre point. Sturdy auxiliary cutting edges support the advance and thus permit sustained high performance and constant precision.

##### Advantage:

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4×4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

##### Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

#### Technical description

Flute length	400 mm
Ø	32 mm
overall length	450 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus

Type of product

Masonry drill