

Garant**Carbide-tipped hammer drill set, Drill Ø: 5-12mm****Order data**

Order number	789045 5-12
GTIN	4062406135898
Item class	71C

Description**Version:**

Drill head with square cross-section. **4x90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially shaped reinforced protection**: protects the engagement of the reinforcements and increases the working life.

Advantage:

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4x4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

Content:

Hammer drill No. 789040: 1 pc. each
size 5; 6; 8 length 110 mm;
size 6; 8; 10; 12 length 160 mm
Presented in: Plastic case

Technical description

Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

Accessories

Carbide-tipped hammer drill SDS-plus Ø×overall length 10X160 mm	789040 10X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 12X160 mm	789040 12X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X110 mm	789040 8X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 6X110 mm	789040 6X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 5X110 mm	789040 5X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X160 mm	789040 8X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 6X160 mm	789040 6X160