

**LED cordless lamp 0 version without battery, 12 V, Type: GLI12330****Order data**

Order number	073203 GLI12330
GTIN	3165140741750
Item class	03B

Description**Version:**

12 V work light with 10 LEDs and two brightness levels. Adjustable angle up to 200°, suspension hook, carabiner and integral magnet.

Supplied with:

Cordless lamp without battery and without charger.

Note:

Suitable spare batteries and chargers can be found under No. 073851– 073866.

suitable battery - supplier / battery type / voltage: Bosch 12 V

Manufacturer's designation: GLI 12-330

Illumination: 330 lm

Number of rechargeable batteries contained: 0

Type of rechargeable battery: Lithium-ion

Battery voltage: 12 V

Technical description

Battery voltage	12 V
Manufacturer's designation	GLI 12-330

Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	300 g
Power supply	Rechargeable battery-powered
Illumination	330 lm
Pivot range	0 - 200 degrees
ATEX zone	no
Product name attribute	12 V
suitable battery - supplier / battery type / voltage	Bosch 12 V
Type of product	Work lamp

Accessories

Li-ion battery Battery type, battery voltage B12 V	073855 B12
Li-ion battery Battery type, battery voltage B12 V	073851 B12
Battery charger Type AL1130CV	073866 AL1130CV