



Cordless sabre saw, Type: M18ONESX-9



Order data

Order number	078220 M18ONESX-9
GTIN	4002395287956
Item class	03L

Description

Version:

Milwaukee cordless sabre saw for working in difficult-to-access areas.

- **Electronic controls with steplessly variable stroke length and overload protection.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**
- **ONE-KEY™ technology. Complete individualisation of tool settings thanks to Bluetooth™ connection to the Milwaukee® ONE-KEY™ app.**
- **Controllable soft start for maximum speed and control.**
- **The motor brake stops the saw blade automatically as it leaves the material on completion of the cut.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**
- **Electronic control of rate of strokes, orbital stroke can be switched off.**
- **Stroke optimisation to suit the material, ensures longer working life of the saw blades.**
- **AVS anti-vibration system and patented eccentric gearbox for very smooth running.**
- **Kick-back protection system to protect the gearbox against kick-backs from the workpiece.**

Supplied with:

Supplied with a carrying case / carrying wallet, 2 batteries, quick charger and saw blade.

Note:

Sabre saw blades can be found from No. 588600.

See No. 073810; 073811; 073814; 073815; 073816; 073829 for suitable spare batteries and chargers.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type HB 18 V

App link: OneKey

Manufacturer's designation: M18ONESX-902X

Number of rechargeable batteries contained: 2
 Type of rechargeable battery: Lithium-ion
 Battery capacity: 9 Ah
 Battery voltage: 18 V
 Stroke length: 28.6 mm

Technical description

Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	15.9 m/s ²
Special features	FIXTEC
Battery capacity	9 Ah
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Manufacturer's designation	M18ONESX-902X
Weight	4 kg
Battery voltage	18 V
Stroke length	28.6 mm
Rate of strokes	0 - 3000 rpm
App link	OneKey
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
Li-ion system M18B2 Battery type, battery voltage MB18 V	073827 MB18
Battery starter set High Output™ Type M18HNRG3	073826 M18HNRG3

Battery starter set High Output™ Type M18HNRG55	073830 M18HNRG55
Battery starter set High Output™ Type M18HNRG8	073831 M18HNRG8
Battery starter set High Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion battery High Output™ Battery type, battery voltage MHB3 V	073808 MHB3
Li-ion battery High Output™ Battery type, battery voltage MHB55 V	073809 MHB55
Li-ion battery High Output™ Battery type, battery voltage MHB8 V	073810 MHB8
Li-ion battery High Output™ Rechargeable battery type, battery voltage MHB12 V	073811 MHB12