

**RENISHAW****Stylus, ruby ball Length 20 mm, Contact point Ø D: 2,5mm**

## Order data

Order number	494222 2,5
GTIN	2050002041028
Item class	49F

## Description

**Version:**

Ruby-tipped probe with M2 connection thread

**Note:**

Further styli with other sizes and shank types available on request.

## Technical description

Contact point Ø D	2.5 mm
Weight	0.4 g
Shank Ø S	1.4 mm
Material of shank	Steel
effective working length	16.4 mm
Length L	20 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes