

Garant GRIDLINE

Wall cabinet with Plain sheet metal sliding doors, Width in G: 80



Order data

Order number	943905 80
GTIN	4062406136192
Item class	9GI

Description

Version:

Mountings for storage shelves at 25-mm intervals. Rear panel with \square 9×9 mm holes at 37-mm intervals for mounting Easyfix hooks and supports. Can be locked by 2-component Haptoprene® handle using a cylinder lock. Available with closed rear wall if required. Cable pass-through at the top of the cabinet. With centre partition. Suitable storage shelves No. 943914 size 40.

Supplied with:

Cabinet supplied with storage shelf and fastenings.

Colour:

Body light grey RAL 7035, doorsanthracite RAL 7016, **powder-coated.**

Note:

Different walls may require different fastenings. The customer should check requirements before installation. See No. 943914 for individual storage shelves.

Technical description

ComfortClose	no
Depth	400 mm
Usable width	1950 mm
Number of shelves	2
Usable height	463 mm
Width	2000 mm

Electronic locking system can be retrofitted	yes
Usable depth	325 mm
Height	600 mm
Weight	66 kg
Depth in G	16
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	65 kg
Cabinet housing internal load capacity	250 kg
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Wall cabinet

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Additional shelf for wall cabinets for cabinet / compartment width in G 40	943914 40
Lock plate for GridLine Type GP21	914227 GP21