

Garant GRIDLINE

Wall cabinet with Viewing window swing doors, Width in G: 30**Order data**

Order number	943903 30
GTIN	4062406136161
Item class	9GI

Description**Version:**

Mountings for storage shelves at 25-mm intervals. Rear panel with \square 9×9 mm holes at 37-mm intervals for mounting Easyfix hooks and supports. Can be locked by 2-component Haptoprene® handle using a cylinder lock. Available with closed rear wall if required. Cable pass-through at the top of the cabinet.

Supplied with:

Cabinet supplied with storage shelf and fastenings.

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

Different walls may require different fastenings. The customer should check requirements before installation. See No. 943914 for individual storage shelves.

Technical description

Depth	400 mm
Usable height	445 mm
Usable width	700 mm

ComfortClose	no
Electronic locking system can be retrofitted	yes
Height	600 mm
Width	750 mm
Usable depth	325 mm
Weight	25 kg
Number of shelves	1
Depth in G	16
Width in G	30
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	65 kg
Cabinet housing internal load capacity	250 kg
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Wall cabinet

Accessories

Additional shelf for wall cabinets for cabinet / compartment width in G 30	943914 30
Slide handle for GridLine Type GP11	914226 GP11
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F