

**Garant****Shelving cabinet without doors, Height: 2000mm****Order data**

Order number	944009 2000
GTIN	4062406136444
Item class	9GI

**Description****Version:**

Mountings for storage shelves at 25-mm intervals.

Equipped shelf cabinet in 30×11G.

**Fitted with:**

Number of storage bins: 30 × No. 963321 size SB6; 30 × No. 963321 size SB5; 20× No. 963321 size SB4

**Supplied with:**

Cabinet with shelves and open storage bins.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated.**

**Note:**

- **For single open storage bins see No 963321.**
- **For individual storage shelves see No. 944061, 944065.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Weight	82 kg
Usable height	1845 mm
Number of shelves	9
Width	750 mm
Depth	275 mm
Electronic locking system can be retrofitted	no
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Height	2000 mm
Cabinet fronts	open
Width in G	30
Depth in G	11
Material thickness	0.9 mm
Cabinet housing internal load capacity	500 kg
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard

## Accessories

Storage shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944061 30
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Stepped shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944065 30