



## Cordless impact wrench / impact driver, Type: M12FID



### Order data

Order number	074014 M12FID
GTIN	4058546029951
Item class	03L

### Description

#### Version:

- Robust and powerful FUEL™ cordless impact wrench with brushless POWERSTATE™ EC motor.
- Long motor service life and high energy efficiency.
- Sturdy metal gearbox casing and ergonomic central handle with soft-grip coating.
- Battery charge display.
- LED illumination of the working area.
- Reversible, with electronic speed control.
- REDLINK PLUS™ electronics – for unique power management.
- DRIVE CONTROL™ permits quick switching between the available settings with different speeds and torques.

Compact impact wrench (130 mm long) with 1/4 inch HEX bit holder.

#### Advantage:

FUEL™ top model.

#### Supplied with:

Supplied with charger and HD box.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Manufacturer's designation: M12FID-202X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion  
 Battery capacity: 2 A·h  
 Battery voltage: 12 V  
 maximum torque 1st step: 147 N·m

### Technical description

Tool arbor size	1/4 in
Battery voltage	12 V
Manufacturer's designation	M12FID-202X
maximum screw Ø (8.8 - 12.9)	M14
Number of impacts 1st stage	0 - 4000 min <sup>-1</sup>
typical application	Strong
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Tool arbor drive profile	HEX (E 6.3)
Packaging	Modular case (HD=Heavy Duty)
Battery capacity	2 A·h
Weight	1.1 kg
maximum vibration to EN	1.5 m/s <sup>2</sup>
maximum torque 1st step	147 N·m
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

### Accessories

Li-ion system M4B2/M12B2 Rechargeable battery type,  
 battery voltage MB12 V

073814 MB12