



Cordless impact wrench / impact driver, Type: M12FIWF12



Order data

Order number	074014 M12FIWF12
GTIN	4058546225612
Item class	03L

Description

Version:

- Robust and powerful FUEL™ cordless impact screwdriver with brushless POWERSTATE™ EC motor.
- Long motor service life and high energy efficiency.
- Sturdy metal gearbox casing and ergonomic central handle with soft-grip coating.
- Battery charge display.
- LED illumination of the working area.
- Reversible, with electronic speed control.
- REDLINK PLUS™ electronics – for unique power management.
- DRIVE CONTROL™ permits quick switching between the available settings with different speeds and torques.

With snap ring.

Advantage:

FUEL™ top model.

Supplied with:

Supplied with 2× Li-ion high-power batteries, charger, HD box.

Technical description

Manufacturer's designation	M12FIWF12-422X
Tool arbor size	1/2 in
Weight	1.1 kg
Number of impacts 3rd stage	0 - 3200 min ⁻¹
maximum torque 1st step	339 Nm
Number of impacts 1st stage	0 - 1100 min ⁻¹
Battery voltage	12 V
Tool arbor drive profile	External square drive
Number of impacts 2nd stage	0 - 2100 min ⁻¹
maximum screw Ø (8.8 - 12.9)	M16
Battery capacity	2 Ah
Battery capacity	4 Ah
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	1.5 m/s ²
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
typical application	Heavy Duty
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion system M12B4 Battery type MB12	073815 MB12
---------------------------------------	-------------