



Cordless hammer drill, Type: M18CHPX-9



Order data

Order number	075530 M18CHPX-9
GTIN	4002395162192
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **SDS plus chuck.**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**
- **FIXTEC tool quick-change system for switching between the SDS-Plus chuck and the quick-release metal drill chuck, without using tools.**
- **Zero rotation for easy chisel work.**
- **Safety clutch protects user and machine if the drill jams.**
- **AVS anti-vibration system.**

Supplied with:

Supplied with FIXTEC SDS-plus adapter, quick-change chuck 1.5 – 13 mm, additional handle with depth stop, quick charger, 2 × 18V batteries, carrying case

Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18CHPX-902X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 9 Ah
 Battery voltage: 18 V
 Speed range: 0 - 1350 rpm

Technical description

maximum twist drill size Ø in concrete	28 mm
Packaging	Modular case (HD=Heavy Duty)
Tool arbor shape	SDS-Plus
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum hammer rate	5000 rpm
Impact energy	4 J
Battery capacity	9 Ah
maximum twist drill size Ø in wood	30 mm
Weight	4.3 kg
Manufacturer's designation	M18CHPX-902X
maximum twist drill size Ø in steel	13 mm
Battery voltage	18 V
Speed range	0 - 1350 rpm
maximum vibration to EN	8.6 m/s ²
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Hammer drill

Accessories

Li-ion battery High Output™ Battery type, battery voltage MHB3 V	073808 MHB3
--	-------------

Li-ion battery High Output™ Battery type, battery voltage MHB55 V	073809 MHB55
---	--------------

Li-ion battery High Output™ Battery type, battery voltage MHB8 V	073810 MHB8
Li-ion battery High Output™ Rechargeable battery type, battery voltage MHB12 V	073811 MHB12
Battery starter set High Output™ Type M18HNRG3	073826 M18HNRG3
Battery starter set High Output™ Type M18HNRG55	073830 M18HNRG55
Battery starter set High Output™ Type M18HNRG8	073831 M18HNRG8
Battery starter set High Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
Li-ion system M18B2 Battery type, battery voltage MB18 V	073827 MB18
Battery starter set Type M18NRG5	073839 M18NRG5
Battery charger Type M1218FC	073840 M1218FC
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10
Carbide-tipped multi-purpose drill set long Drill Ø 6-12 mm	787055 6-12
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787000 10
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787000 12
Carbide-tipped multi-purpose drill Drill Ø 3 mm	787000 3
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787000 4
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787000 5
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787000 6
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787000 8
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 12 mm	787060 12
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 6 mm	787060 6
	787060 8

Carbide-tipped multi-purpose drill long with SDS-plus
shank socket Drill Ø 8 mm

Carbide-tipped multi-purpose drill set Number of drills 7

787010 7