



## Shoe, black VD 3500 SST SF ESD, S3 NB, EU shoe size: 37



### Order data

Order number	092662 37
GTIN	4044348590140
Item class	09C

### Description

#### Version:

Safety shoe with VARIO Multiflex® technology for less shoe weight.

- **Upper material of ultra-light and smooth micro-fibres.**
- **Breathable functional lining.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**

• **Protection against electrostatic discharge (ESD).**

VARIO DYNAMICS SST safety shoe with heat-resistant (up to approx. 220°C) and **particularly anti-slip Perbunan outer sole** (SST-STEITZ SURE STEP).

- **Perbunan Athletic SST outer sole, silver grey.**

Shoes and lace-up boots with textile penetration protection.

#### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

#### Note:

Wide version XB, see No. 092663.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

Material of protective toe-cap	Aluminium
EU shoe size	37
Puncture resistance	Tekstil
Cold insulation	down to -20°C
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Protection class	S3
Standard	Inlay type-tested according to DGUV regulation 191
Gender	Unisex
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes