

Garant
Cutting disc, X-LOCK high-performance version EXTRA THIN, STAINLESS STEEL, Disc Ø: 125mm

Order data

Order number	563273 125
GTIN	4062406151720
Item class	51M

Description
Version:

Special type for **stainless steel**.

New **high-performance version** using state of the art technology with significant productivity advantages and excellent cutting qualities. **Increased cutting performance** due to rough free-grinding side faces; **improved service life**.

The thinness of the disc allows **very quick** cutting **with low force and optimum time saving**.

Clean cut edges, virtually no burrs.

Quick disc changing without using tools using the X-LOCK System.

Specification:

A60R-BF.

Note:

X-LOCK cutting discs are upwards-compatible and can also be used on conventional angle grinders.

Technical description

Disc Ø	125 mm
--------	--------

Disc thickness	1 mm
Shape description	flat
Bore Ø	22.23 mm
Specification	A60R-BF
Series	X-LOCK system
for material thicknesses	3 - 5 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	Steel
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		

Plastic, GRP	suitable only under restricted conditions
Uni	suitable only under restricted conditions
dry	suitable