



Cordless hammer drill, Type: M18FHM



Order data

Order number	075530 M18FHM
GTIN	4058546228392
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

M18 FUEL™ SDS-MAX cordless rotary hammer with brushless POWERSTATE™ motor. REDLINK PLUS™ electronics with new High-Output™ 12.0 Ah battery.

Integral **ONE-KEY™** technology and stop switch for continuous operation. Long anti-vibration back handle minimises vibration.

Advantage:

ONE-KEY™ technology.

Supplied with:

Supplied with charger, 1× 18 V / 12 Ah High-Output battery, case.

Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Technical description

Manufacturer's designation	M18FHM-121C
----------------------------	-------------

maximum hammer rate	2900 min ⁻¹
Tool arbor shape	SDS Max
Battery voltage	18 V
Battery capacity	12 Ah
Impact energy	11 J
Shank	SDS Max
Speed range	0 - 380 min ⁻¹
maximum vibration to EN	9.4 m/s ²
Packaging	Carrying case
Weight	10.2 kg
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
maximum twist drill size Ø in concrete	45 mm
App link	OneKey
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Carbide-tipped multi-purpose drilllong with SDS-plus shank socket Drill Ø 12 mm	787060 12
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8
Li-ion system M18B2 Battery type MB18	073827 MB18

Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8
Battery charger Type M1218C	073840 M1218C
Carbide-tipped multi-purpose drill setlong Drill Ø 6-12 mm	787055 6-12
Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Battery starter setHigh Output™ Battery type M18HNRG3	073826 M18HNRG3
Battery starter setHigh Output™ Type M18HNRG55	073830 M18HNRG55
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10
Battery charger Type M1218FC	073840 M1218FC
Li-ion batteryHigh Output™ Battery type MHB3	073808 MHB3
Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Carbide-tipped multi-purpose drilllong with SDS-plus shank socket Drill Ø 8 mm	787060 8
Battery starter set Type M18NRG5	073839 M18NRG5
Carbide-tipped multi-purpose drilllong with SDS-plus shank socket Drill Ø 10 mm	787060 10
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12