



Cordless random orbital sander with rechargeable battery, Type: M18BOS125



Order data

Order number	077319 M18BOS125
GTIN	4058546221744
Item class	03L

Description

Version:

M18 cordless random orbital sander 6-step pre-set speed settings for removal rate appropriate for the material. Dust box with integrated filter. 100% system-compatible with the Milwaukee® M18™ product range. 8-hole backing pad for efficient extraction.

Supplied with:

Supplied with 2x5.0 Ah Li-ion battery, dust bag, extraction adapter, extension adapter, 2x abrasive paper.

Note:

Suitable 8-hole abrasive disc item No. 567745 and ABRANET item No. 567802.

Technical description

Speed of oscillation	14000 - 24000 min ⁻¹
Orbital stroke	2.4 mm
Manufacturer's designation	M18BOS125-502B
Backing pad Ø	125 mm
Weight	1.6 kg
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

Battery voltage	18 V
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	2
Battery capacity	5 Ah
Type of rechargeable battery	Lithium-ion
Packaging	Carrying case
Type of product	Orbital sander

Accessories

Li-ion system M18B2 Battery type MB18	073827 MB18
Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8
Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion batteryHigh Output™ Battery type MHB3	073808 MHB3
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery starter setHigh Output™ Battery type M18HNRG3	073826 M18HNRG3
Battery starter setHigh Output™ Type M18HNRG55	073830 M18HNRG55
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12
Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8
Paper velour-backed abrasive disc (A)8 holes Grit 120	567745 120
Paper velour-backed abrasive disc (A)8 holes Grit 180	567745 180
Paper velour-backed abrasive disc (A)8 holes Grit 240	567745 240
Paper velour-backed abrasive disc (A)8 holes Grit 320	567745 320
Paper velour-backed abrasive disc (A)8 holes Grit 40	567745 40
Paper velour-backed abrasive disc (A)8 holes Grit 400	567745 400
Paper velour-backed abrasive disc (A)8 holes Grit 60	567745 60
Paper velour-backed abrasive disc (A)8 holes Grit 600	567745 600

Paper velour-backed abrasive disc (A)8 holes Grit 80	567745 80
Paper velour-backed abrasive disc (A)8 holes Grit 800	567745 800