



Cordless angle grinder 18 V, Type: M18FLAG



Order data

Order number	077135 M18FLAG
GTIN	4058546220600
Item class	03L

Description

Version:

Cordless two-hand angle grinder Ø 230 mm. Version with a dead man's switch and restart inhibit.

The latest generation of the brushless POWERSTATE™ motor (powered by only a single 18 V / 12 Ah High Output™ battery pack)

Supplied with:

Supplied with 1 pc. 18 V / 12 Ah **High Output™** Li-ion battery, charger M12-18 FC, safety guard piece, AVS side handle, Fixtec quick clamping nut, 2 pcs. exchangeable dust-protection grilles, carrying case.

Technical description

maximum cutting depth	65 mm
Battery capacity	12 Ah
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
maximum speed	6600 min ⁻¹
Manufacturer's designation	M18FLAG230XPDB-121C
Battery voltage	18 V
Weight	5.2 kg

maximum vibration to EN	8.7 m/s ²
Restart block	yes
maximum disc Ø	230 mm
Special features	FIXTEC
Special features	Dead man's switch
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Packaging	Carrying case
Power supply	Rechargeable battery-powered
Type of product	Angle grinder

Accessories

Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Li-ion system M18B5 Battery type MB18	073816 MB18
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12
Battery starter setHigh Output™ Type M18HNRG55	073830 M18HNRG55
Li-ion batteryHigh Output™ Battery type MHB3	073808 MHB3
Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8
Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion system M18B2 Battery type MB18	073827 MB18
Battery starter setHigh Output™ Battery type M18HNRG3	073826 M18HNRG3
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8