

**GWX angle grinder, Type: 19-125S****Order data**

Order number	077050 19-125S
GTIN	3165140962490
Item class	03C

Description**Version:**

- **Quick and easy:** Easy change of angle grinder accessories without any parts that could be lost or need for additional tools.
- **No additional wrenches required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** due to 100% quick tool exchange requiring no tools.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Very high user protection thanks to the acoustic signal when fitting is correct.
- **Clean working without annoying scratches!** Less prominent and fewer scuffs with X-LOCK angle grinders.

125-mm angle grinder with 1,900 W motor. **X-Lock system.**

Supplied with:

Including additional vibration control handle, safety guard and package.

Technical description

maximum disc Ø	125 mm
Manufacturer's designation	GWX 19-125 S
Power consumption	1900 W
Weight	2.5 kg

Speed range	2800 - 11500 min ⁻¹
Restart block	yes
Special features	Variable speed; Kickback Control
Packaging	cardboard
Power supply	Mains operated
Series	X-LOCK system
Type of product	Angle grinder