

**Carbide-tipped hammer drill, SDS-max, Øxoverall length: 40X720mm****Order data**

Order number	789204 40X720
GTIN	3165140565851
Item class	76K

Description**Version:****Special carbide insert geometry for longer tool lives.**

TARGET TIP TECHNOLOGY – more severely angled tip: More precise drilling, no slipping on the surface, aggressive drilling in concrete steel and faster drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

Generation SDS-max-7 with embedded carbide cutters, soldered.

Technical description

Ø	40 mm
overall length	720 mm
Flute length	600 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

