

Garant GRIDLINE

TFT monitor housing, Type: 2**Order data**

| | |
|--------------|---------------|
| Order number | 948401 2 |
| GTIN | 4062406151973 |
| Item class | 9GS |

Description**Version:**

TFT monitor housing for flat screens, lockable, with fixed storage shelf. Self-supporting steplessly adjustable lift door with polycarbonate window.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, lift doors RAL 7016 anthracite **powder-coated**.

Technical description

| | |
|-------------------------------------|---------|
| Width | 1250 mm |
| Monitor housing usable depth bottom | 230 mm |
| Monitor housing usable depth top | 150 mm |
| Height | 600 mm |
| Depth top | 200 mm |
| Weight | 36 kg |
| Depth bottom | 275 mm |
| Monitor housing usable width | 1190 mm |

| | |
|-------------------------------|---|
| Monitor housing usable height | 460 mm |
| IP Index of Protection | IP 41 |
| Material thickness | 0.9 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Monitor housing |

Accessories

| | |
|--|-------------|
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Slide handle for garment lockers without cylinder insert | 914221 |